



Catalog No. 9T21C3326G02

Description: 1C,5kVA,480-120/240,115C,N3R,60Hz,QMS

UPC No 783173012079

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
----------	---

Specifications

Phase	1
PriVoltage	480
SecVoltage	120/240
KVA	5 KVA
Coil Material	CU
TempRise	115 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	16350
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes