



**Catalog No. 9T21C3326G80**

**Description:** 1C,3kVA,480-120/240,80C,3R,60Hz,QMS

**UPC No** 783173117408

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

|          |   |
|----------|---|
| Category | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
|----------|---|

**Specifications**

|                |          |
|----------------|----------|
| Phase          | 1        |
| PriVoltage     | 480      |
| SecVoltage     | 120/240  |
| KVA            | 3 KVA    |
| Coil Material  | CU       |
| TempRise       | 80 °C    |
| ElecShield     | N        |
| Sub Type       | Standard |
| Frequency      | 60 Hz    |
| FrameSize      | 16500    |
| TempClass      | 180 °C   |
| AmbTemp        | 40 °C    |
| InsulSys       | IS-12    |
| KFactor        | K1       |
| Enclosure Type | NEMA 3R  |

**Classifications**

|     |     |
|-----|-----|
| UL  | Yes |
| cUL | Yes |