



Catalog No. 9T21C3335

Description: 1C,15kVA,208-240/480,115C,3R,60Hz,QMS

UPC No 783173012222

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

| | |
|----------|---|
| Category | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
|----------|---|

Specifications

| | |
|----------------|----------|
| Phase | 1 |
| PriVoltage | 208 |
| SecVoltage | 240/480 |
| KVA | 15 KVA |
| Coil Material | CU |
| TempRise | 115 °C |
| ElecShield | N |
| Sub Type | Standard |
| Frequency | 60 Hz |
| FrameSize | 1923 |
| TempClass | 180 °C |
| AmbTemp | 40 °C |
| InsulSys | IS-12 |
| KFactor | K1 |
| Enclosure Type | NEMA 3R |

Classifications

| | |
|-----|-----|
| UL | Yes |
| cUL | Yes |

