

Representative Image

## Catalog No. 9T51B0004

**Description: 1C,0.1KVA,240X480-120/240,55C,3R,60HZ,QB**

**UPC No 783173008263**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

### Descriptors

| | |
|---|---|
| Category | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T5 |

### Specifications

| | |
|---|---|
| Phase | 1 |
| PriVoltage | 240x480 |
| SecVoltage | 120/240 |
| KVA | 0.1 KVA |
| Coil Material | CU |
| TempRise | 55 °C |
| ElecShield | N |
| Sub Type | Standard |
| Frequency | 60 Hz |
| FrameSize | 6200 |
| TempClass | 105 °C |
| AmbTemp | 40 °C |
| InsulSys | CLASSA |
| KFactor | K1 |
| Enclosure Type | NEMA 3R |

### Classifications

| | |
|---|---|
| UL | Yes |
| cUL | Yes |