



Representative Image

**Catalog No. 9T51B0004**

**Description: 1C,0.1KVA,240X480-120/240,55C,3R,60HZ,QB**

**UPC No 783173008263**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

**Specifications**

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	0.1 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	6200
TempClass	105 °C
AmbTemp	40 °C
InsulSys	CLASSA
KFactor	K1
Enclosure Type	NEMA 3R

**Classifications**

UL	Yes
cUL	Yes