



**Catalog No. 9T51B0063G03**

**Description: 1C,3kVA,575-120/240,115C,3R,ES,60Hz,QB**

**UPC No 783173242964**

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

**Specifications**

Phase	1
PriVoltage	575
SecVoltage	120/240
KVA	3 KVA
Coil Material	CU
TempRise	115 °C
ElecShield	Y
Frequency	60 Hz
FrameSize	14350
AmbTemp	40 °C
KFactor	K1
Enclosure Type	NEMA 3R

**Classifications**

cUL	No
-----	----