



Representative Image

Catalog No. 9T51B0148

Description: 1C,25KVA,133-120,115C,3R,60HZ,BB,AXF,QB

UPC No 783173036648

Home > Transformers > Dry Type, Encapsulated, Enclosed > Buck Boost Autotransformer

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descripteurs

Catégorie	Buck Boost Autotransformer
GO Schedule	T5

Spécifications

Phase	1
PriVoltage	133
SecVoltage	120
KVA	25 KVA
Coil Material	CU
TempRise	115 °C
ElecShield	N
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
FrameSize	14400
AmbTemp	40 °C
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

cUL	Yes
-----	-----