



Catalog No. 9T51B0511

Description: 1C,1.5KVA,240X480-120/240,100C,3R,5/6,QB

UPC No 783173011843

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	1.5 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Sub Type	Standard
Frequency	50 Hz
FrameSize	14225
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes