



Representative Image

## Catalog No. 9T51B0513

**Description:** 1C,3KVA,240X480-120/240,115C,3R,50/60,QB

**UPC No** 783173011850

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

### Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	3 KVA
Coil Material	CU
TempRise	115 °C
ElecShield	N
Sub Type	Standard
Frequency	50 Hz
FrameSize	14400
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

### Classifications

UL	Yes
cUL	Yes