



Representative Image

Catalog No. 9T51B0570

Description: 1C,1kVA,600(-2 5%)-120/240,100C,3R,QB

UPC No 783173801802

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

| | |
|-------------|---|
| Category | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T5 |

Specifications

| | |
|----------------|----------|
| Phase | 1 |
| PriVoltage | 600 |
| SecVoltage | 120/240 |
| KVA | 1 KVA |
| Coil Material | CU |
| TempRise | 100 °C |
| ElecShield | N |
| Sub Type | Standard |
| Frequency | 50 Hz |
| FrameSize | 12275 |
| TempClass | 180 °C |
| AmbTemp | 40 °C |
| InsulSys | IS-12 |
| KFactor | K1 |
| Enclosure Type | NEMA 3R |

Classifications

| | |
|-----|-----|
| UL | Yes |
| cUL | Yes |