



Representative Image

Catalog No. 9T51B1017

Description: 1C,0.25kVA,240(±2,5%)-110,100,3R,50Hz,QB

UPC No 783173242971

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	228/240/252
SecVoltage	110
KVA	0.25 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Frequency	50 Hz
FrameSize	8200
AmbTemp	40 °C
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

cUL	Yes
-----	-----