

Representative Image

Catalog No. 9T51B1020

Description: 1C,1kVA,252/240/228-110,100C,N3R,50Hz,QB

UPC No 783173238073

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	228/240/252
SecVoltage	110
KVA	1 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Frequency	50 Hz
FrameSize	12275
AmbTemp	40 °C
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

cUL	Yes