



Representative Image

Catalog No. 9T51B1792

Description: 1C,2kVA,480(-2,5%)-277,100C,N3R,60Hz,QB

UPC No 783173123096

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	480
SecVoltage	277
KVA	2 KVA
Coil Material	CU
TempRise	100 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	14250
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes