



Representative Image

Catalog No. 9T51B1831

Description: 1C,0.15kVA,240x480-120,55C,N3R,50Hz,QB

UPC No 783173194683

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120-24
KVA	0.15 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	Standard
Frequency	50 Hz
FrameSize	8175
TempClass	105 °C
AmbTemp	40 °C
InsulSys	CLASSA
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes