



Representative Image

## Catalog No. 9T51B5810

**Description:** 1C,3.9kVA,230-208,80C,3R,QB

**UPC No** 783173066607

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

### Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

### Specifications

Phase	1
PriVoltage	230
SecVoltage	208
KVA	3.9 KVA
Coil Material	CU
TempRise	80 °C
ElecShield	N
Sub Type	Standard
Frequency	50 Hz
FrameSize	10200
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

### Classifications

UL	Yes
cUL	Yes