



Representative Image

Catalog No. 9T58E0156

Description: 1C,0.2kVA,230/400-115/230,55C,C&C,TB,IP

UPC No 783173155530

Home > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool

ABB's CE marked 9T58E control power isolating transformers feature a welded core, encapsulated coils to deliver reliable performance while keeping vibration and noise low. The IP 20 terminal blocks are a standard safety feature ideal for any 50 or 60 Hz applications. These transformers are available with various input and output voltages and kVA ratings. The CE marked 9T58E control power isolating transformers meet domestic and international standards.

Descriptors

| | |
|-------------|--------------|
| Category | Machine Tool |
| GO Schedule | TQ |

Specifications

| | |
|----------------|-------------------|
| Phase | 1 |
| PriVoltage | 230/400 |
| SecVoltage | 115/230 |
| KVA | 0.2 KVA |
| Coil Material | CU |
| TempRise | 55 °C |
| ElecShield | N |
| Sub Type | CE Terminal Block |
| Frequency | 50 Hz |
| FrameSize | 10225 |
| TempClass | 180 °C |
| AmbTemp | 40 °C |
| InsulSys | IS-12 |
| KFactor | K1 |
| Enclosure Type | None |
| PriRatingType | 8 |
| SecRatingType | 8 |
| Outline | 303B947AAP10225 |
| TransType | IP |

Classifications

| | |
|-----|-----|
| UL | Yes |
| cUL | Yes |
| CE | Yes |