



Representative Image

## Catalog No. 9T58E0506

**Description:** 1C,0.25KVA,480>200-120,80C,C&C,CE,IP

**UPC No** 783173825716

**Home > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool**

General purpose encapsulated open core and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.

### Descriptors

Category	Machine Tool
GO Schedule	TQ

### Specifications

Phase	1
PriVoltage	200/400/480
SecVoltage	120
KVA	0.25 KVA
Coil Material	CU
TempRise	80 °C
ElecShield	N
Sub Type	CE Terminal Block
Frequency	50 Hz
FrameSize	10225
AmbTemp	40 °C
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
TransType	IP

### Classifications

cUL	No
CE	Yes