



Representative Image

## Catalog No. 9T58K0065G09

**Description:** 1C,0.15kVA,575>230-115/95,80C,C&C,FC,IP

**UPC No** 783173123256

**Home > Transformers > Dry Type, Encapsulated Core & Coil > Machine Tool**

ABB's Machine tool core and coil transformers are isolation transformers designed to provide a high degree of secondary voltage stability (regulation) during a brief period of overload condition (also referred to as "inrush current"). They are ideal for applications where power regulation and space optimization are critical. Machine tool core and coil transformers feature welded cores to deliver outstanding performance, long life, and quiet operation.

### Descriptors

Category	Machine Tool
GO Schedule	TQ

### Specifications

Phase	1
PriVoltage	230/460/575
SecVoltage	115/95
KVA	0.15 KVA
Coil Material	CU
TempRise	80 °C
ElecShield	N
Sub Type	Machine Tool Terminal Blk
Frequency	50 Hz
FrameSize	8200
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
SecRatingType	1
Outline	303B947AAP08200
TransType	IP

### Classifications

UL	Yes
cUL	Yes