



Representative Image

Catalog No. 9T58K0504

Description: 1C,0.15kVA,480-120,55C,C&C,CLO,60Hz,IP

UPC No 783173202203

Home > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

General purpose encapsulated open core and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	480
SecVoltage	120
KVA	0.15 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	CONTROL LEADS OUT
Frequency	60 Hz
FrameSize	8150
AmbTemp	40 °C
KFactor	K1
Enclosure Type	None
FuseHolder	NONE
PriRatingType	8
SecRatingType	8
TransType	IP

Classifications

cUL	No
-----	----