



**Catalog No. 9T58K0947**

**Description:** 1C,0.5kVA,600-208,115C,C&C,50/60HZ,TB,IP

**UPC No** 783173238202

**Home > Transformers > Dry Type, Encapsulated Core & Coil > Control Power**

General purpose encapsulated open core and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.

**Descriptors**

Category	Control Power
GO Schedule	TQ

**Specifications**

Phase	1
PriVoltage	600
SecVoltage	208
KVA	0.5 KVA
Coil Material	CU
TempRise	115 °C
ElecShield	N
Sub Type	Encapsulated
Frequency	50 Hz
FrameSize	10225
AmbTemp	40 °C
KFactor	K1
Enclosure Type	None
FuseHolder	NONE
PriRatingType	8
SecRatingType	8
TransType	IP

**Classifications**

cUL	Yes
-----	-----