



Representative Image

Catalog No. 9T58K0953G38

Description: 1C,0.1KVA,416>380-110/220,55C,C&C,2CC,IP

UPC No 783173195796

Home > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

General purpose encapsulated open core and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	380/400/416
SecVoltage	110/220
KVA	0.1 KVA
Coil Material	CU
TempRise	55 °C
ElecShield	N
Sub Type	Control Terminal Block
Frequency	50 Hz
FrameSize	8150
AmbTemp	40 °C
KFactor	K1
Enclosure Type	None
FuseHolder	(2) CC + (1) MIDGET
PriRatingType	8
SecRatingType	8
TransType	IP

Classifications

cUL	Yes
-----	-----