

Catalog No. 9T58K4084

Description: 1C,0.3kVA,115/230-43,80C,50/60Hz,LO,IP

UPC No 783173123898

Home > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

ABB's General purpose encapsulated open core, and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.



Representative Image

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	115/230
SecVoltage	43
KVA	0.3 KVA
Coil Material	CU
TempRise	80 °C
ElecShield	N
Sub Type	CONTROL LEADS OUT
Frequency	50 Hz
FrameSize	10225
TempClass	180 °C
AmbTemp	40 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	None
PriRatingType	8
SecRatingType	8
Outline	303B947ABP10225
TransType	IP

Classifications

UL	Yes
cUL	Yes