



**Catalog No. 9T85B3874G15**

**Description: 3A,75kVA,480-208Y/120,115C,N3R,K1,TENV**

**UPC No 783173224199**

**Home > Transformers > Dry Type Non-Ventilated > Totally Enclosed, Non-Ventilated (TENV)**

ABB's Totally enclosed non-ventilated (TENV) transformers are a smart choice for applications where dry-type transformer benefits are desired but the standard enclosure openings are unacceptable because of adverse atmospheric conditions. TENV transformers are recommended where dust, dirt, or lint may be present or where transformers are subject to sprays or controlled wash-down conditions. They are UL Listed through 75kVA for indoor or protected outdoor applications. TENV transformers meet NEMA TP-1 efficiency.

**Descriptors**

Category	Totally Enclosed, Non-Ventilated (TENV)
GO Schedule	TA

**Specifications**

Phase	3
PriVoltage	480
SecVoltage	208Y/120
KVA	75 KVA
Coil Material	AL
TempRise	115 °C
ElecShield	N
Frequency	60 Hz
Impedance	4.5 %
FrameSize	XV375
AmbTemp	40 °C
EnergyEfficiency	NEMA TP 1
KFactor	K1
Enclosure Type	TENV
Sound	Std

**Classifications**

cUL	No
CE	No

