



Catalog No. AQU3182RCXAXB4

Description: PRO-STK 240V 3PH 225A NFT 18CR CU

UPC No 783175408658

Home > Panelboards > ReliaGear Lighting Panel > Pro-Stock Lighting Panel

ReliaGear Pro-Stock panelboards offer a symmetrical design for top or bottom feed with main breaker or main lugs. With a reversible interior, there is no need to specify top or bottom feed. Modular kits are available from inventory for immediate availability to your customers in over 1,500 panel designs. Main bus ratings of 250 A and 400 A main breaker; 225 A, 400 A and 600A main lug available.

Descriptors

Category	Pro-Stock Lighting Panel
GO Schedule	32

Specifications

Voltage	240 V
Phase	3
Panel Rating	225
No of Circuits	18
Feed Thru	No
Bus	Copper
Interior Type	AQU
Box/Front Height	31.500 in
Interior Description	Pro-Stock 240V, 3PH, 225A 18Cir. CU
GSA Compliance	No