



Catalog No. CGB192-G

Description: PVCCTD CORDCONN .125-.25 HUB1/2IN G

UPC No 704508360016

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Cord Connector, 1/2 Inch, Cord Range Diameter .125-.250, Inside Body Diameter .625, Gray, Steel Body, Aluminum Gland Nut, Neoprene Bushing

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	0.125-0.250 Inch
Material	Steel Body, Aluminum Glandnut
Color	Gray
NEMA Rating	3R

Classifications

Brand Name	Ocal
Standard	UL E23223

Dimensions

Size	1/2 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Suitable for cable diameter	3.175-6.35 mm
Material	Metal

by ABB

ETIM	EC000441 Cable gland
Material quality	Steel
Surface protection	Other
Colour	Light grey
Model	Straight