

Catalog No. CGB294-G

Description: PVC CTD CORD CONN HUB 3/4IN GRY

UPC No 704508360306

Home > Cable Protection Systems > Ocal > Cable gland connector

PVC Coated Cord Connector, 3/4 Inch, Cord Range Diameter .375-.500, Inside Body Diameter .688, Gray, Steel Body, Aluminum Gland Nut, Neoprene Bushing

Descriptors

Category	Cable gland connector
Special Features	PVC Coated for Corrosion Resistance
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead

Specifications

Conductor Range	0.375-0.500 Inch
Material	Steel Body, Aluminum Glandnut
Color	Gray
NEMA Rating	3R

Classifications

Brand Name	Ocal
Standard	UL E23223

Dimensions

Size	3/4 Inch

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000441 Cable gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Suitable for cable diameter	9.525-12.70 mm
Material	Metal
Material quality	Steel

ETIM	EC000441 Cable gland
Surface protection	Other
Colour	Light grey
Model	Straight