



**Catalog No. CI08-FCI02**

**Description:** CONNECTOR INTERFACE NC08 TO FCI 2 W

**UPC No** 5020963024412

**Home > Cable Protection Systems > Harnessflex > Electrical connector assembly**

Hinged Connector Interface Fitting, Straight, 2-Way FCI Automotive Apex 2.8 Connector to Conduit, Conduit Size NC08/NW7.5, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

**Descriptors**

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

**Specifications**

Connection	Straight, 2-way connection
Material	Polyamide/Nylon
Color	Black
Insulation	IP40
Temperature Rating	-40 to 120 C
Environmental Conditions	Very High UV Protection

**Classifications**

Brand Name	Harnessflex
Standard	RoHS Compliant

**Dimensions**

Size	Conduit Size NC08/NW7.5
------	-------------------------

**Compliance and Certifications**

RoHS	RoHS3 Compliant
------	-----------------