



Catalog No. CIH08-DT3

Description: High Temp Interface NC08 - DT 3

UPC No 5020963804281

Home > Cable Protection Systems > Harnessflex > Electrical connector assembly

Hinged Connector Interface Fitting for High Temperatures, Straight, 3-Way Deutsch DT Connector to Conduit, Conduit Size NC08/NW7.5, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

Descriptors

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

Specifications

Connection	Straight, 3-way connection
Material	Polyamide/Nylon
Color	Dark Orange
Insulation	IP40
Temperature Rating	-40 to 185 C
Environmental Conditions	Medium UV Protection

Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant

Dimensions

Size	Conduit Size NC08/NW7.5
------	-------------------------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------