



Catalog No. CIH12-FCI14

Description: High Temp Interface NC12 to FCI 14

UPC No 5020963804250

Home > Cable Protection Systems > Harnessflex > Electrical connector assembly

Hinged Connector Interface Fitting for High Temperatures, Straight, 14-Way FCI APex Automotive Connector to Conduit, Conduit Size NC12/NW10, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

Descriptors

Category	Electrical connector assembly
Special Features	High Pull-Off Strength
Application	Provide Connection Between Connector Interface and Conduit

Specifications

Connection	Straight, 14-way connection
Material	Polyamide/Nylon
Color	Dark Orange
Insulation	IP40
Temperature Rating	-40 to 185 C
Environmental Conditions	Medium UV Protection

Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant

Dimensions

Size	Conduit Size NC16/NW13
------	------------------------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------