



Representative Image

Catalog No. COND1-GST

Description: PVC CTD COND 1IN RGD STL GRY

UPC No 704508029913

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 1 Inch/27 Metric, Outside Diameter with PVC 1.40 Inch/35.40 Millimeters, Nominal Wall Thickness with PVC .17 Inch/4.21 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	1 in
Outside Diameter	1.40 in , 35.40 mm
Inside Diameter	1.06 in , 27.00 mm
Length	9.91 ft , 3.02 m
Wall Thickness	0.17 in , 4.21 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001179 Protective metallic hose
Nominal size in inch	1 inch

by ABB

ETIM	EC001179 Protective metallic hose
Outer diameter	35.4 mm
Inner diameter	33.4 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid