



Representative Image

Catalog No. COND11/2-GST

Description: PVC CTD COND 1-1/2IN RGD STL GRY

UPC No 704508029937

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 1-1/2 Inch/41 Metric, Outside Diameter with PVC 1.98 Inch/50.20 Millimeters, Nominal Wall Thickness with PVC .18 Inch/4.52 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	1-1/2 in
Outside Diameter	1.98 in , 50.20 mm
Inside Diameter	1.62 in , 41.20 mm
Length	9.91 ft , 3.02 m
Wall Thickness	0.18 in , 4.52 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001179 Protective metallic hose
Nominal size in inch	1 1/2 inch

by ABB

ETIM	EC001179 Protective metallic hose
Outer diameter	50.2 mm
Inner diameter	48.3 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid