



Representative Image

Catalog No. COND11/4-GST

Description: PVC CTD COND 1-1/4IN RGD STL GRY

UPC No 704508029920

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 1-1/4 Inch/35 Metric, Outside Diameter with PVC 1.74 Inch/44.10 Millimeters, Nominal Wall Thickness with PVC .17 Inch/4.39 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	1-1/4 in
Outside Diameter	1.74 in , 44.10 mm
Inside Diameter	1.39 in , 35.40 mm
Length	9.91 ft , 3.02 m
Wall Thickness	0.17 in , 4.39 mm

ETIM	EC001179 Protective metallic hose
Nominal size in inch	1 1/4 inch
Outer diameter	44.1 mm
Inner diameter	42.2 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid

by ABB