



Representative Image

Catalog No. COND2-GST

Description: PVC CTD COND 2IN RGD STL GRY

UPC No 704508029944

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 2 Inch/53 Metric, Outside Diameter with PVC 2.46 Inch/62.30 Millimeters, Nominal Wall Thickness with PVC .19 Inch/4.72 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	2 in
Outside Diameter	2.46 in , 62.30 mm
Inside Diameter	2.08 in , 52.90 mm
Length	9.91 ft , 3.02 m
Wall Thickness	0.19 in , 4.72 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001179 Protective metallic hose
Nominal size in inch	2 inch

by ABB

ETIM	EC001179 Protective metallic hose
Outer diameter	62.3 mm
Inner diameter	60.3 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid