



Representative Image

Catalog No. COND21/2-GST

Description: PVC CTD COND 2-1/2IN RGD STL GRY

UPC No 704508030889

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 2-1/2 Inch/63 Metric, Outside Diameter with PVC 2.96 Inch/75.00 Millimeters, Nominal Wall Thickness with PVC .23 Inch/5.91 Millimeters, Length without Couplings 9 Feet 10-1/2 Inch/3.01 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	2-1/2 in
Outside Diameter	2.96 in , 75.00 mm
Inside Diameter	2.49 in , 63.20 mm
Length	9.875 ft , 3.01 m
Wall Thickness	0.23 in , 5.91 mm

ETIM	EC001179 Protective metallic hose
Nominal size in inch	2 1/2 inch
Outer diameter	75 mm
Inner diameter	73 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid

by ABB