

Representative Image

## Catalog No. COND3/4-GN

**Description: PVC CTD COND 3/4IN RGD STL GREEN**

**UPC No 704508028459**

**Home > Cable Protection Systems > Ocal > Electrical conduit**

PVC Coated Conduit, Pipe Size 3/4 Inch/21 Metric, Outside Diameter with PVC 1.13 Inch/28.70 Millimeters, Nominal Wall Thickness with PVC .139 Inch/3.53 Millimeters, Length without Couplings 9 Feet 11-1/4 Inch /3.03 Meters, Hot-dip Galvanized Steel, Green

### Descriptors

| | |
|---|---|
| Category | Electrical conduit |
| Special Features | Color-Coded Thread Protectors |
| Application | Corrosion Protection for Electrical Systems |

### Specifications

| | |
|---|---|
| Material | Steel |
| Finish | Hot-Dip Galvanized |
| Color | Green |

### Classifications

| | |
|---|---|
| Brand Name | Ocal |
| Standard | cULus E46453, CSA |

### Dimensions

| | |
|---|---|
| Trade Size | 3/4 in |
| Outside Diameter | 1.13 in , 28.70 mm |
| Inside Diameter | 0.84 in , 21.20 mm |
| Length | 9.94 ft , 3.03 m |
| Wall Thickness | 0.139 in , 3.53 mm |

| | |
|---|---|
| ETIM | EC001179 Protective metallic hose |
| Nominal size in inch | 3/4 inch |
| Outer diameter | 28.7 mm |
| Inner diameter | 26.7 mm |
| Material | Steel |
| Surface protection | Other |
| Colour | Green |
| Bending strength | Rigid |

by ABB