



Representative Image

Catalog No. COND3/4-GST

Description: PVC CTD COND 3/4IN RGD STL GRY

UPC No 704508029906

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 3/4 Inch/21 Metric, Outside Diameter with PVC 1.13 Inch/28.70 Millimeters, Nominal Wall Thickness with PVC .139 Inch/3.53 Millimeters, Length without Couplings 9 Feet 11-1/4 Inch /3.03 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	3/4 in
Outside Diameter	1.13 in , 28.70 mm
Inside Diameter	0.84 in , 21.20 mm
Length	9.94 ft , 3.03 m
Wall Thickness	0.139 in , 3.53 mm

ETIM	EC001179 Protective metallic hose
Nominal size in inch	3/4 inch
Outer diameter	28.7 mm
Inner diameter	26.7 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid

by ABB