



Representative Image

Catalog No. COND3-GST

Description: PVC CTD COND 3IN RGD STL GRY

UPC No 704508029951

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 3 Inch/78 Metric, Outside Diameter with PVC 3.58 Inch/90.90 Millimeters, Nominal Wall Thickness with PVC .25 Inch/6.22 Millimeters, Length without Couplings 9 Feet 10-1/2 Inch /3.01 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	3 in , 78 mm
Outside Diameter	3.58 in , 90.90 mm
Inside Diameter	3.09 in , 78.50 mm
Length	9.875 ft , 3.01 m
Wall Thickness	0.25 in , 6.22 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001179 Protective metallic hose
Nominal size in inch	3 inch

by ABB

ETIM	EC001179 Protective metallic hose
Outer diameter	90.9 mm
Inner diameter	88.9 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid