

Representative Image

Catalog No. COND31/2-GST

Description: PVC CTD COND 3-1/2IN RGD STL GRY

UPC No 704508029968

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 3-1/2 Inch/91 Metric, Outside Diameter with PVC 1.08 Inch/103.60 Millimeters, Nominal Wall Thickness with PVC .26 Inch/6.47 Millimeters, Length without Couplings 9 Feet 10-1/4 Inch /3.00 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	3/4 in
Outside Diameter	1.08 in , 103.60 mm
Inside Diameter	3.57 in , 90.70 mm
Length	9.85 ft , 3 m
Wall Thickness	0.26 in , 6.47 mm

ETIM	EC001179 Protective metallic hose
Nominal size in inch	3 1/2 inch
Outer diameter	103.6 mm
Inner diameter	101.6 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid