

## Catalog No. COND31/2-GST

**Description:** PVC CTD COND 3-1/2IN RGD STL GRY

**UPC No** 704508029968

**Home > Cable Protection Systems > Ocal > Electrical conduit**

PVC Coated Conduit, Pipe Size 3-1/2 Inch/91 Metric, Outside Diameter with PVC 1.08 Inch/103.60 Millimeters, Nominal Wall Thickness with PVC .26 Inch/6.47 Millimeters, Length without Couplings 9 Feet 10-1/4 Inch /3.00 Meters, Hot-dip Galvanized Rigid Steel, Gray

Representative Image

### Descriptors

|                  |                                             |
|------------------|---------------------------------------------|
| Category         | Electrical conduit                          |
| Special Features | Color-Coded Thread Protectors               |
| Application      | Corrosion Protection for Electrical Systems |

### Specifications

|          |                    |
|----------|--------------------|
| Material | Steel              |
| Finish   | Hot-Dip Galvanized |
| Color    | Gray               |

### Classifications

|            |                   |
|------------|-------------------|
| Brand Name | Ocal              |
| Standard   | cULus E46453, CSA |

### Dimensions

|                  |                     |
|------------------|---------------------|
| Trade Size       | 3/4 in              |
| Outside Diameter | 1.08 in , 103.60 mm |
| Inside Diameter  | 3.57 in , 90.70 mm  |
| Length           | 9.85 ft , 3 m       |
| Wall Thickness   | 0.26 in , 6.47 mm   |

|                      |                                   |
|----------------------|-----------------------------------|
| ETIM                 | EC001179 Protective metallic hose |
| Nominal size in inch | 3 1/2 inch                        |
| Outer diameter       | 103.6 mm                          |
| Inner diameter       | 101.6 mm                          |
| Material             | Steel                             |
| Surface protection   | Other                             |
| Colour               | Grey                              |
| Bending strength     | Rigid                             |

**by ABB**