



Representative Image

Catalog No. COND4-GST

Description: PVC CTD COND 4IN RGD STL GRY

UPC No 704508029975

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 4 Inch/103 Metric, Outside Diameter with PVC 4.58 Inch/116.30 Millimeters, Nominal Wall Thickness with PVC .27 Inch/6.73 Millimeters, Length without Couplings 9 Feet 10-1/4 Inch /3.00 Meters, Hot-dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	4 in , 103 mm
Outside Diameter	4.58 in , 116.30 mm
Inside Diameter	4.05 in , 12.90 mm
Length	9.85 ft , 3 m
Wall Thickness	0.27 in , 6.73 mm

ETIM	EC001179 Protective metallic hose
Nominal size in inch	4 inch
Outer diameter	116.3 mm
Inner diameter	114.3 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid

by ABB