



Representative Image

Catalog No. COND5-G

Description: PVC CTD COND 5IN RGD STL GRAY

UPC No 704508261122

Home > Cable Protection Systems > Ocal > Electrical conduit

PVC Coated Conduit, Pipe Size 5 Inch/129 Metric, Outside Diameter with PVC 5.64 Inch/143.30 Millimeters, Nominal Wall Thickness with PVC .29 Inch/7.23 Millimeters, Length without Couplings 9 Feet 10 Inch /3.00 Meters, Hot-dip Galvanized Steel, Gray

Descriptors

Category	Electrical conduit
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems

Specifications

Material	Steel
Finish	Hot-Dip Galvanized
Color	Gray

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Trade Size	5 in , 129 mm
Outside Diameter	5.64 in , 143.30 mm
Inside Diameter	5.07 in , 128.90 mm
Length	9-1/12 ft , 3 m
Wall Thickness	0.29 in , 7.23 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001179 Protective metallic hose
Nominal size in inch	Other

by ABB

ETIM	EC001179 Protective metallic hose
Outer diameter	143.3 mm
Inner diameter	141.3 mm
Material	Steel
Surface protection	Other
Colour	Grey
Bending strength	Rigid