



Catalog No. CPC12/50M

Description: 12MM SOLID PE CONDUIT 50M - BL

UPC No 5020963785856

Home > Cable Protection Systems > Harnessflex > Flexible Non-Metallic Conduit

Flame Retardant, Highly Flexible Conduit, NC Size 12/NW Size 10, Outside Diameter 13.0mm, Inside Diameter 9.4mm, Static Bend Radius 25mm, Very High UV Resistance and Fatigue Life, IP40 Rating, FR Co-Polyester, Reel Length 50 Meters, Black

Descriptors

Category	Flexible Non-Metallic Conduit
Application	Ideal for Harness Applications Such as Engine, Body Section and Chassis. CPC is Resistant to Hydrocarbons, Greases, Fuels and Oils

Specifications

Radius	Static: 25 mm
Flexibility	Very High
Material	Fire Resistant Co-Polyester
Color	Black

Classifications

Brand Name	Harnessflex
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV) EU200/53/EC

Dimensions

Trade Size	NC12/NW10
Outside Diameter	13 mm
Inside Diameter	9.4 mm
Length	50 m

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	12 mm
Nominal size in inch	5/16 inch
Outer diameter	13 mm
Inner diameter	9.4 mm
Material	Other
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	V2
Bending radius, static	25 mm
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Halogen free	Y