

Representative Image

Catalog No. CPL1SA-G

Description: PVC CTD COND CPLG 1IN ALUM GRAY

UPC No 704508362386

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Conduit Coupling, 1 Inch/27 Metric Coupling Size, 1.91 Inch/48.41 Millimeters Minimum Length of Metal, 4.94 Inch/139.70 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Aluminum, Gray

Descriptors

Category	Electrical conduit coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections

Specifications

Material	Aluminum
Color	Gray

Classifications

Brand Name	Ocal

Dimensions

Trade Size	1 in , 27 mm
Length	4.94 in , 139.7 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Model	Thread
For nominal tube diameter	27 mm
Two piece	N
With inspection opening and cover	N