



Representative Image

Catalog No. CPL2-GN

Description: PVC CTD COND CPLG 2IN RGD STL GREEN

UPC No 704508028497

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Conduit Coupling, 2 Inch/53 Metric Coupling Size, 1.94 Inch/49.19 Millimeters Minimum Length of Metal, 5.94 Inch/150.79 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Galvanized Rigid Steel, Green

Descriptors

Category	Electrical conduit coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections

Specifications

Material	Steel
Color	Green

Classifications

Brand Name	Ocal
------------	------

Dimensions

Trade Size	2 in , 53 mm
Length	5.94 in , 150.79 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Continuously galvanized
Model	Thread
For nominal tube diameter	53 mm
Two piece	N
With inspection opening and cover	N

by ABB