



Representative Image

Catalog No. CPL3/4-GN

Description: PVC CTD COND CPLG 3/4IN STL GREEN

UPC No 704508028480

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Conduit Coupling, 3/4 Inch/21 Metric Coupling Size, 1.53 Inch/38.91 Millimeters Minimum Length of Metal, 3.75 Inch/95.25 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Galvanized Rigid Steel, Green

Descriptors

Category	Electrical conduit coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections

Specifications

Material	Steel
Color	Green

Classifications

Brand Name	Ocal
------------	------

Dimensions

Trade Size	3/4 in , 21 mm
Length	3.75 in , 95.25 mm

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Continuously galvanized
Model	Thread
For nominal tube diameter	21 mm
Two piece	N
With inspection opening and cover	N