



Representative Image

Catalog No. CPL4-GPVC

Description: PVC CTD COND CPLG 4IN NO INT CTD GR

UPC No 704508015213

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Conduit Coupling, 4 Inch/103 Metric Coupling Size, 3.19 Inch/80.97 Millimeters Minimum Length of Metal, 7.19 Inch/182.57 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, No Internal Coating, Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections

Specifications

Material	Steel
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Trade Size	4 in , 103 mm
Length	7.19 in , 182.57 mm

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Continuously galvanized
Model	Thread
For nominal tube diameter	103 mm
Two piece	N
With inspection opening and cover	N