



Representative Image

Catalog No. CPL5-G

Description: PVC CTD COND CPLG 5IN STL GRAY

UPC No 704508362829

Home > Cable Protection Systems > Ocal > Electrical conduit coupling

PVC Coated Conduit Coupling, 5 Inch/129 Metric Coupling Size, 3.37 Inch/85.69 Millimeters Minimum Length of Metal, 7.37 Inch/187.29 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections

Specifications

Material	Steel
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Trade Size	5 in , 129 mm
Length	7.37 in , 187.29 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Continuously galvanized
Model	Thread
For nominal tube diameter	129 mm
Two piece	N

by ABB

ETIM	EC000939 Coupler for installation tubes
With inspection opening and cover	N