

Representative Image

## Catalog No. CPS422020

**Description: CONNECTOR SHROUD(422020)**

**UPC No 5020963022982**

**Home > Cable Protection Systems > Adaptaflex > Electrical conduit coupling**

Hinged Protective Shroud, Straight, Conduit Size A: NC20/NW17, Side B: NC20/NW17, Internal Diameter 43mm, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

### Descriptors

| | |
|---|---|
| Category | Electrical conduit coupling |
| Application | Protection for In-Line Connectors, Fuse Links, Circuit Breakers and Splicing Areas |

### Specifications

| | |
|---|---|
| Installation Type | Externally Hinged |
| Material | Polyamide/Nylon |
| Color | Black |

### Classifications

| | |
|---|---|
| Brand Name | Harnessflex |
| Standard | RoHS Compliant, Complies with End of Life Vehicle (ELV) Directive EU 2000/53/EC |

### Dimensions

| | |
|---|---|
| Trade Size | NC20/NW17 |
| Inside Diameter | 43 mm |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |

| | |
|---|---|
| ETIM | EC001172 Coupler for corrugated plastic hoses |
| Material | Plastic |
| Material quality | Polyamide (PA) |
| Degree of protection (IP) | IP40 |
| Model | Straight |
| Nominal size | 20-20 mm |
| Colour | Black |

by ABB