



Representative Image

Catalog No. CPS422020

Description: CONNECTOR SHROUD(422020)

UPC No 5020963022982

Home > Cable Protection Systems > Adaptaflex > Electrical conduit coupling

Hinged Protective Shroud, Straight, Conduit Size A: NC20/NW17, Side B: NC20/NW17, Internal Diameter 43mm, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

Descriptors

Category	Electrical conduit coupling
Application	Protection for In-Line Connectors, Fuse Links, Circuit Breakers and Splicing Areas

Specifications

Installation Type	Externally Hinged
Material	Polyamide/Nylon
Color	Black

Classifications

Brand Name	Harnessflex
Standard	RoHS Compliant, Complies with End of Life Vehicle (ELV) Directive EU 2000/53/EC

Dimensions

Trade Size	NC20/NW17
Inside Diameter	43 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	Straight
Nominal size	20-20 mm
Colour	Black

by ABB