



**Catalog No. CR305J102ADA**

**Description:**

**UPC No**

**Home > Contactors & Starters > NEMA Contactors > 300 Line Full Voltage Magnetic Contactors**

Contactors, NEMA, Full Voltage, Non-Reversing, NEMA Size: 0, Maximum Voltage: 600 VAC, Amp Rating: 18 Amp, Horsepower Rating: 1 @ 115 VAC, Coil Voltage: 115 VAC @ 60 Hz, Enclosure Type: NEMA Type 1, Dimensions: 6 Inch W x 10 Inch H x 4.63 Inch D, Features: Supplied with 1 Normally Open Auxiliary Contact 02ADA

**Descriptors**

Category	300 Line Full Voltage Magnetic Contactors
GO Schedule	10G

**Specifications**

Continuous Current	20 A
Enclosure Type	NEMA Type 1
Horsepower	1.00 hp